



800 Series II Stationary Single Screw Vertical Mixer Specifications

The name customers have entrusted for material handling solutions since 1948!

	U/M	270 Low Profile	350
CAPACITY			
Mixing	ft ³ (m ³)	270 (7.6)	350 (9.9)
w/Optional Extension	ft ³ (m ³)	335 (9.5)	425 (12)
UNIT			
Empty Wt.	lb (kg)	5,995 (2719)	6,446 (2924)
Max. Load @ 25lb/cu.ft.	lb (kg)	6,750 (3062)	8,750 (3969)
Max. Gross Wt.	lb (kg)	12,745 (5781)	15,196 (6893)
No. of Screws (See Options below)		1	1
Overall Length	in (m)	132-1/8 (3.4)	146-5/8 (3.7)
Overall Height without Guard	in (m)	84-7/8 (2.2)	90-5/8 (2.3)
Overall Height with Top Guard	in (m)	91-1/2 (2.3)	97-1/2 (2.5)
Overall Height with 12 in. Ext.	in (m)	103-1/2 (2.6)	109-1/2 (2.8)
Overall Width	in (m)	103-5/8 (2.7)	112-3/4 (2.9)
Screw Flighting Thickness	in (mm)	1/2 (13)	1/2 (13)
Floor Thickness	in (mm)	1/2 (13)	1/2 (13)
Sidewall Thickness	in (mm)	1/4 (6)	1/4 (6)
Horsepower Requirements		(2) 7½ or (2) 10 HP or (1) 15 HP or (1) 20 HP (1) 25 HP or (1) 30 HP or (1) 40 HP or (1) 50 HP	
Restrictors		2	2
Hour Meter		Std.	Std.
Scale System		3-Point	3-Point
DOOR OPENINGS			
Right Side, Left Side, Both			
Height	in (mm)	39 (991)	39 (991)
Width	in (mm)	34 (864)	34 (864)
Back Door, Hydraulic			
Height	in (mm)	30 (762)	30 (762)
Width	in (mm)	34 (864)	34 (864)
OPTIONS			
Tru Taper™ Vertical Mixer Screw Cone Top with Dual Kicker (not included in basic unit)		Choose One Size Screw for Your Mixing Needs	
Maximum No. of Knives‡		5	7
Manual or Hydraulic Door Control		Right Side or Left Side	Right Side or Left Side
Discharge Chute with or without Magnet		Opt.	Opt.
Tub Mounted Magnet+		Opt.	Opt.
Wide Selection of Indicators		dinamica generale®, Weigh-Tronix®, & Digi-Star®	
Ladder		Opt.	Opt.
Variable Frequency Drive Pkg. (VFD)		Opt.	Opt.

+ Patent Pending.

‡ Quantity varies with material in ration and processing time.

Options include:

DIG IN with the RAPTOR™*!




*Patented

3 Sizes Available!

Engineered to complement our standard knives, this AR knife features a forward-facing design to dig in, hook, and slice bales faster and more aggressively!

PROTECT WHAT MATTERS with a Tub Mounted Magnet*!



270 cu. ft.

350 cu. ft.

Exclusive to Patz!

Encased in stainless steel, this magnet is mounted only into a Patz Vertical Mixer tub wall on a hinged assembly for effective removal of tramp metal from rations.

Actual tramp metal removed from magnet.

*Patent Pending

Proven Performance you can count on!

Watch video online
Patz - A Good Partner.



CAUTION: Never operate Patz equipment without all shields and guards in place. **Safety Is No Accident.** Before operating any piece of equipment, be sure to read and understand the operator's manual. This manual should be kept with the machine at all times. Additionally, make sure all safety shields and devices are functioning properly and are securely in place. Specifications and prices subject to change without notice.